



A-Shape LED

18A21/LED/927/P/E26/ND 4/2FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light		0.5 s
Nominal lifetime	10,950 hour(s)	Power Factor (Fraction)		0.7
Switching Cycle	50,000	Voltage (Nom)		120 V
Lighting Technology	LED	Temperature		
EU RoHS compliant	Yes	T-Case Maximum (Nom)		167 °F
Light Technical		Controls and Dimming		
Color Code	927	Dimmable		No
Beam Angle (Nom)	250 degree(s)	Mechanical and Housing		
Luminous Flux	1,500 lm	Bulb Finish		Frosted
Color Designation	Warm White (WW)	Bulb Material		Plastic
Correlated Color Temperature (Nom)	2700 K	Bulb Shape		A21 [A 21mm]
Luminous Efficacy (rated) (Nom)	83.00 lm/W	Approval and Application		
Color Consistency	<4	Energy Consumption kWh/1000 h		- kWh
Color rendering index (CRI)	90	Product Data		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order product name		18A21/LED/927/P/E26/ND 4/2FB T20
Operating and Electrical		Full product name		18A21/LED/927/P/E26/ND 4/2FB T20
Line Frequency	60 Hz	Order code		531772
Input Frequency	60 Hz	Material Nr. (12NC)		929001825823
Power Consumption	18 W			
Lamp Current (Nom)	160 mA			
Wattage Equivalent	100 W			

A-Shape LED

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677531775
Numerator - Packs per outer box	4



EAN/UPC - Case	50046677531770
----------------	----------------

Dimensional drawing




Product	D	C
18A21/LED/927/P/E26/ND 4/2FB T20	3-1/8 inch	5-9/16 inch

Photometric data



Spectral Power Distribution Colour - 18A21/LED/927/P/E26/ND 4/2FB T20


General uniform lighting - 18A21/LED/927/P/E26/ND 4/2FB T20




Light Distribution Diagram - 18A21/LED/927/P/E26/ND 4/2FB T20

A-Shape LED

Lifetime



Life Expectancy Diagram - 18A21/LED/927/P/E26/ND 4/2FB T20



Lumen Maintenance Diagram - 18A21/LED/927/P/E26/ND 4/2FB T20

