

LED InstantFit Lamps

14T8/COR/48-840/MF18/G 1/4 FFP

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal Lifetime (Nom)	36000 h
Switching Cycle	50000X
B50L70	36000 h
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	240 °
Luminous Flux (Nom)	1800 lm
Luminous Flux (Rated) (Nom)	1800 lm
Rated Beam Angle	240 °
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	14 W
Lamp Current (Max)	130 mA
Lamp Current (Min)	47 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9


Voltage (Nom)	120-277 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Product Data	
Order product name	14T8/COR/48-840/MF18/G 1/4 FFP
EAN/UPC - Product	50046677538373
Order code	929001845663
Numerator - Quantity Per Pack	1

LED InstantFit Lamps

Numerator - Packs per outer box	1
Material Nr. (12NC)	929001845663
Net Weight (Piece)	0.063 kg

Warnings and Safety


Dimensional drawing




TLED IF CorePro 4ft 1800lm 4000K

Product	D1	D2	A1	A2	A3
14T8/COR/48-840/MF18/G 1/4	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
FFP					


Photometric data



LEDtube 14W G13 840 ND BB18




LEDtube 14W G13 830 ND BB17




LEDtube 14W G13 840 ND BB18

LED InstantFit Lamps


Lifetime




LEDtube 14W G13 830-850 ND BB17-18




LEDtube 14W G13 830-850 ND BB17-18



LEDtube 14W G13 830-850 ND BB17-18



LEDtube 14W G13 830-850 ND BB17-18



LEDtube 14W G13 830-850 ND BB17-18

LED InstantFit Lamps

