



LED Highbay

100HB/LED/740/ND WB DL BB 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General Information	
Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	100-250W
Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	130 °
Initial lumen (Nom)	12000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	100 W
Lamp Current (Nom)	850 mA
Wattage Equivalent	250 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V

Temperature	
T-Case Maximum (Nom)	70 °C


Controls and Dimming	
Dimmable	No

Approval and Application	
Energy Certifications	DLC Standard

Product Data	
Order product name	100HB/LED/740/ND WB DL BB 2/1
EAN/UPC - Product	046677478001
Order code	478008
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001851404
Net Weight (Piece)	0.885 kg

LED Highbay



Dimensional drawing



High Bay Mains 250W 4000K Down Light WB

Product	D	C
100HB/LED/740/ND WB DL BB 2/1	211 mm	252 mm


Photometric data



General technical drawing

TrueForce LED Industrial and Retail WB



TrueForce LED Industrial and Retail 100HB 740 WB



TrueForce LED Industrial and Retail 740

LED Highbay

Lifetime



LED TForce HB MV 120-100W E40 others 840 12D ND NB

LED TForce HB MV 120-100W E40 others 840 12D ND NB

