



LED PAR38

16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	1,250 lm
Luminous Intensity (Nom)	2,700 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	16.5 W
Lamp Current (Nom)	170 mA


Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	194 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20

LED PAR38

Full product name	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20
Order code	534867
Material Nr. (12NC)	929001853804
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	046677534868
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677534863

Dimensional drawing




Product	D	C
16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	4-3/4 inch	5-5/16 inch

Photometric data



Accent Lighting Spots - 16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20


Light Distribution Diagram - 16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20




Spectral Power Distribution Colour - 16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20

LED PAR38

Lifetime



Life Expectancy Diagram - 16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20



Lumen Maintenance Diagram - 16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20

