



LED PAR30 S/L

11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information		Wattage Equivalent	
Cap-Base	E26 [Single Contact Medium Screw]	75 W	
Nominal lifetime	25,000 hour(s)	Starting Time (Nom)	
Switching Cycle	50,000	0.5 s	
Lighting Technology	LED	Warm-up time to 60% light	
EU RoHS compliant	Yes	0.5 s	
Light Technical		Power Factor (Fraction)	
Color Code	930 [CCT of 3000K]	0.9	
Beam Angle (Nom)	40 degree(s)	Voltage (Nom)	
Luminous Flux	850 lm	120 V	
Luminous Intensity (Nom)	2,000 cd	Temperature	
Color Designation	White (WH)	T-Case Maximum (Nom)	
Correlated Color Temperature (Nom)	3000 K	185 °F	
Luminous Efficacy (rated) (Nom)	75.00 lm/W	Controls and Dimming	
Color Consistency	<4	Dimmable	
Color rendering index (CRI)	90	Yes	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Mechanical and Housing	
Operating and Electrical		Bulb Finish	
Line Frequency	60 Hz	Clear	
Input Frequency	60 Hz	Bulb Material	
Power Consumption	11.3 W	Plastic	
Lamp Current (Nom)	120 mA	Bulb Shape	
		PAR30L [PAR 3.75 inch/95mm Long]	
		Approval and Application	
		Suitable For Accent Lighting	
		Yes	
		Energy Consumption kWh/1000 h	
		- kWh	
		Product Data	
		Order product name	
		11.3PAR30L/PER/930/F40/DIM/120V	
		6/1FBT20	

LED PAR30 S/L

Full product name	11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20
Order code	535427
Material Nr. (12NC)	929001854004
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	046677535421
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677535426

Dimensional drawing




Product	D	C
11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20	3-3/4 inch	4-5/8 inch


Photometric data



Light Distribution Diagram - 11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20



Spectral Power Distribution Colour - 11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20




Accent Lighting Spots - 11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20



Lumen Maintenance Diagram - 11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20

