



LED PAR30 S/L

11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	11.3-75W
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	40 °
Initial lumen (Nom)	850 lm
Luminous Intensity (Nom)	2000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	11.3 W
Lamp Current (Nom)	120 mA
Wattage Equivalent	75 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	85 °C


Controls and Dimming	
Dimmable	Yes

Approval and Application	
Suitable For Accent Lighting	Yes

Product Data	
Order product name	11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20
EAN/UPC - Product	046677535421
Order code	535427
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001854004
Net Weight (Piece)	0.285 kg

LED PAR30 S/L


Dimensional drawing




PAR30L 120V 13-90W 950lm 40D 3000K E26

Product	D	C
11.3PAR30L/PER/930/F40/DIM/120V 6/1FBT20	94.8 mm	116.1 mm


Photometric data



LEDspot E26 40°




LEDspot E26



LEDspot PAR30L E26 40°

LED PAR30 S/L

Lifetime



LEDspot E26

LEDspot E26

