



# A-Shape LED

## 42A40/LED/865/FR/P/E26E39/ND 4/1FB

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	42-300W

Light Technical	
Color Code	865 [ CCT of 6500K]
Beam Angle (Nom)	150 °
Luminous Flux (Nom)	5000 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	119.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	42 W
Lamp Current (Nom)	370 mA
Wattage Equivalent	300 W
Starting Time (Nom)	1 s

Warm Up Time to 60% Light (Nom)	1 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	85 °C


Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted

Product Data	
Order product name	42A40/LED/865/FR/P/E26E39/ND 4/1FB
EAN/UPC - Product	046677479305
Order code	479303
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001854915
Net Weight (Piece)	0.710 kg

# A-Shape LED


## Dimensional drawing




Bulb A125 120V 45-300W 5000lm 6500K E26

Product	D	C
42A40/LED/865/FR/P/E26E39/ND 4/1FB	125 mm	265 mm


## Photometric data



LEDbulb 42W A40 E26 865 15D ND





LEDbulb 42W A40 E26 865 15D ND



LEDbulb 42W A40 E26 865 15D ND

# A-Shape LED

## Lifetime



LEDbulb 20W A30 E26 865 15D ND

LEDbulb 20W A30 E26 865 15D ND

