



# A-Shape LED

## 9A19/LED/950/P/E26/ND 6/1FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	10,950 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	250 degree(s)
Luminous Flux	800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	88.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	9 W
Lamp Current (Nom)	85 mA
Wattage Equivalent	60 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	167 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19 [A 19mm]


Approval and Application	
Energy Consumption kWh/1000 h	- kWh

Product Data	
Order product name	9A19/LED/950/P/E26/ND 6/1FB T20
Full product name	9A19/LED/950/P/E26/ND 6/1FB T20
Order code	479971
Material Nr. (12NC)	929001860104
Numerator - Quantity Per Pack	1


## A-Shape LED

EAN/UPC - Product/Case	046677479978
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677479973

## Dimensional drawing




## Photometric data



Product	D	C
9A19/LED/950/P/E26/ND 6/1FB T20	2-7/16 inch	4-1/4 inch

## General Uniform Lighting




CalcuLix Photometrics 4.5

Philip Lighting B.V.


Page 1/1

General uniform lighting - 9A19/LED/950/P/E26/ND 6/1FB T20




A-Shape LED

Lifetime



Life Expectancy Diagram - 9A19/LED/950/P/E26/ND 6/1FB T20



Lumen Maintenance Diagram - 9A19/LED/950/P/E26/ND 6/1FB T20

