



# MASTER LEDbulb

## MASTER LED bulb DT 12-75WE27 927-922 A67 FR

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	100000X
Technical type	12-75W
Light Technical	
Colour Code	922-927 [ CCT of 2,200 K-2,700 K]
Technical Beam Angle (Nom)	200 °
Lamp Luminous Flux 25°C EL (Nom)	1055 lm
Colour Designation	Warm white (WW)
Lamp Luminous Efficacy EM (Nom)	87.00 lm/W
Colour consistency	<6
Colour Rendering Index, horiz (Nom)	90
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz

Power (Rated) (Nom)	12 W
Lamp current (nom.)	68 mA
Wattage equivalent	75 W
Starting time (nom.)	0.1 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Frosted
Approval and Application	
Energy efficiency label (EEL)	A+


# MASTER LEDbulb

Energy Consumption kWh/1000 h	12 kWh
<b>Product Data</b>	
Full product code	871869682618800
Order product name	MASTER LED bulb DT 12-75WE27 927-922 A67 FR
EAN/UPC – product	8718696826188

Order code	929001868602
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001868602
Net weight (piece)	0.104 kg

## Warnings and Safety


## Dimensional drawing




A67 snow core 12-75W 2200-2700K E27 D

Product	D	C
MASTER LED bulb DT 12-75WE27 927-922 A67 FR	77 mm	142 mm

## Photometric data




LEDbulb MAS 12-75W E27 A67 Frosted 927-922 20D DIM



LEDbulb MAS 12-75W E27 A67 Frosted 927-922 20D DIM


# MASTER LEDbulb

## Photometric data




LEDbulb MAS 12-75W E27 A67 Frosted 927-922 20D DIM

## Lifetime



LEDbulb MAS 12-75W E27 A67 Frosted 927-922 20D DIM



LEDbulb MAS 12-75W E27 A67 Frosted 927-922 20D DIM

