



# CorePro LED tube Universal T8

## CorePro LEDtube UN 1200mm HO 18W830 T8

The new Philips CorePro LEDtube Universal T8 brings simplicity to your lighting project. You can forget about the driver technology. Thanks to a unique design, the Philips CorePro LEDtube Universal T8 directly fits into luminaires operating either on Electro Magnetic ballasts, HF Electronic ballasts or mains power connections. So simple to operate and no need to carry double stock of products! Perfectly safe, reliable and easy to install, the Philips CorePro LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes to save energy and reduce investment.

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	30000 h
Switching cycle	50000X

Light Technical	
Colour code	830 [ CCT of 3,000 K]
Beam Angle (Nom)	240 °
Luminous flux (nom.)	1850 lm
Correlated Colour Temperature (Nom)	3000 K
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	18 W

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.97
Voltage (Nom)	220-240 V

Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	65 °C

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb material	Glass

# CorePro LED tube Universal T8

Product length	1200 mm
<b>Approval and Application</b>	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	18 kWh
<b>Product Data</b>	
Full product code	871869680166600

Order product name	CorePro LEDtube UN 1200mm HO 18W830 T8
EAN/UPC – product	8718696801666
Order code	80166600
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001869202
Net weight (piece)	0.270 kg


## Dimensional drawing




TLED 1200mm UNV16W-36W 2100lm 3000K

Product	D1	D2	A1	A2	A3
CorePro LEDtube UN 1200mm HO 18W830 T8	27.9 mm	28 mm	1199.4 mm	1205.3 mm	1213.6 mm

## Photometric data



18W G13



18W G13 830 3000K

# CorePro LED tube Universal T8

## Photometric data




18W G13 830 3000K


## Lifetime



18W G13



18W G13




18W G13



18W G13

# CorePro LED tube Universal T8

## Lifetime



18W G13

