



CorePro LED tube Universal T8

CorePro LEDtube UN 1200mm HO 18W830 T8

The new Philips CorePro LEDtube Universal T8 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips CorePro LEDtube Universal T8 directly fits in luminaires operating either on Electro Magnetic ballasts or HF Electronic ballasts or mains power connection. So simple to operate and no need to carry double stock of products! Perfectly safe, reliable & easy to install Philips CorePro LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes to save energy and lower investment.

Product data

General Information		Power (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		18 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	30000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.97
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	240 °	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	1850 lm	T-Storage (Max)	65 °C
Correlated Color Temperature (Nom)	3000 K	T-Storage (Min)	-40 °C
Color Consistency	<6	T-Case Maximum (Nom)	65 °C
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Controls and Dimming	
		Dimmable	No
Operating and Electrical			
Input Frequency	50 to 60 Hz		

CorePro LED tube Universal T8

Mechanical and Housing

Bulb Material	Glass
Product Length	1200 mm


Approval and Application

Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	18 kWh

Product Data

Full product code	871869680166600
Order product name	CorePro LEDtube UN 1200mm HO 18W830 T8
EAN/UPC - Product	8718696801666
Order code	929001869202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001869202
Net Weight (Piece)	0.270 kg


Dimensional drawing




TLED 1200mm UNV16W-36W 2100lm 3000K

Product	D1	D2	A1	A2	A3
CorePro LEDtube UN 1200mm HO 18W830 T8	27.9 mm	28 mm	1199.4 mm	1205.3 mm	1213.6 mm

Photometric data



18W G13



18W G13 830 3000K

CorePro LED tube Universal T8

Photometric data



18W G13 830 3000K

Lifetime



18W G13



18W G13



18W G13



18W G13

CorePro LED tube Universal T8

Lifetime



18W G13

