PHILIPS

Lighting



LED MR16

7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB

Philips LED MR-16 lamps with single optic technology provide the look and color quality of traditional halogens while using a fraction of the energy. A perfect fit for spot lighting, they are compatible with most existing fixtures with MR16 GU5.3 holders and are designed as a retrofit replacement for halogen or incandescent spots.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	480 lm
Luminous Intensity (Nom)	2,330 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	61.00 lm/W
Color Consistency	<3
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	7.8 W
Lamp Current (Nom)	880 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V

Temperature	
T-Case Maximum (Nom)	105 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Aluminum
Bulb Shape	MR16 [2inch/50mm]

Approval and Application	
Suitable For Accent Lighting	Yes

LED MR16


Energy Consumption kWh/1000 h	- kWh

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677470173
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677470178

Product Data


Order product name	7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB
Full product name	7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB
Order code	470179
Material Nr. (12NC)	929001872904

Dimensional drawing




Product	D	C
7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB	51 mm	46 mm


Photometric data



Light Distribution Diagram - 7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB




Spectral Power Distribution Colour - 7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB




Accent Lighting Spots - 7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB

LED MR16

Lifetime



Life Expectancy Diagram - 7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB



Lumen Maintenance Diagram - 7.8MR16/PER/930/F25/Dim/EC/12V 10/1FB

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.