




# MASTER Value Decorative LED bulbs

## LED classic-giant 40W E27 G200 GOLD DIM

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

### Product data

| General Information                |                    |
|------------------------------------|--------------------|
| Cap-Base                           | E27 [E27]          |
| Nominal lifetime                   | 15,000 hour(s)     |
| Switching Cycle                    | 20,000             |
| Rated Lifetime (Hours)             | 15,000 hour(s)     |
| Lighting Technology                | LED                |
| EU RoHS compliant                  | Yes                |
| Light Technical                    |                    |
| Color Code                         | 820 [CCT of 2000K] |
| Color Code                         | 820 [CCT of 2000K] |
| Luminous Flux                      | 470 lm             |
| Color Designation                  | Flame              |
| Correlated Color Temperature (Nom) | 2000 K             |
| Luminous Efficacy (rated) (Nom)    | 72.00 lm/W         |
| Color Consistency                  | <6                 |
| Color rendering index (CRI)        | 80                 |


| LLMF At End Of Nominal Lifetime (Nom) | 70 %  |
|---------------------------------------|-------|
| Operating and Electrical              |       |
| Line Frequency                        | 50 Hz |
| Input Frequency                       | 50 Hz |
| Power Consumption                     | 6.5 W |
| Lamp Current (Nom)                    | 40 mA |
| Wattage Equivalent                    | 40 W  |
| Starting Time (Nom)                   | 0.5 s |
| Warm-up time to 60% light             | 0.5 s |
| Power Factor (Fraction)               | 0.7   |
| Voltage (Nom)                         | 230 V |
| Temperature                           |       |
| T-Case Maximum (Nom)                  | 45 °C |

MASTER Value Decorative LED bulbs

|                               |                                         |
|-------------------------------|-----------------------------------------|
| Controls and Dimming          |                                         |
| Dimmable                      | Yes                                     |
| Mechanical and Housing        |                                         |
| Bulb Finish                   | Transparent amber                       |
| Bulb Shape                    | G200 [G 200mm]                          |
| Approval and Application      |                                         |
| Energy Consumption kWh/1000 h | 7 kWh                                   |
| EyeComfort                    | Yes                                     |
| Product Data                  |                                         |
| Order product name            | LED classic-giant 40W E27 G200 GOLD DIM |


|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Full product name               | LED classic-giant 40W E27 G200 GOLD DIM |
| Full product code               | 871869680347900                         |
| Order code                      | 929001873401                            |
| Material Nr. (12NC)             | 929001873401                            |
| Numerator - Quantity Per Pack   | 1                                       |
| EAN/UPC - Product/Case          | 8718696803479                           |
| Numerator - Packs per outer box | 2                                       |
| EAN/UPC - Case                  | 8718696803486                           |

Dimensional drawing




| Product                                 | D      | C      |
|-----------------------------------------|--------|--------|
| LED classic-giant 40W E27 G200 GOLD DIM | 200 mm | 286 mm |

Photometric data




Spectral Power Distribution Colour - LED classic-giant 40W E27 G200 GOLD DIM



Light Distribution Diagram - LED classic-giant 40W E27 G200 GOLD DIM


MASTER Value Decorative LED bulbs

Photometric data




General uniform lighting - LED classic-giant 40W E27 G200 GOLD DIM

Lifetime



Lumen Maintenance Diagram - LED classic-giant 40W E27 G200 GOLD DIM



Life Expectancy Diagram - LED classic-giant 40W E27 G200 GOLD DIM

