





## CorePro LEDtube 1200mm HO 18W 865 T8

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pack back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

#### Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.

#### **Product data**

General Information			
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		
Nominal lifetime	50,000 hour(s)		
Switching Cycle	200,000		
Lighting Technology	LED		
Flux measurement reference	Sphere		
CE mark	Yes		
EU RoHS compliant	Yes		


Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	2,000 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	111 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Datasheet, 2024, March 15 data subject to change

Flickering value (PstLM) - Flickering value as	1			
per EN 61000-3-3				
Stroboscopic effect visibility measure (SVM)	0.9			
Photobiological safety according to EN 62471	RG0			
Operating and Electrical				
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz			
Power Consumption	18 W			
Lamp Current (Nom)	90 mA			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			
Voltage (Nom)	220-240 V			
LED alternative to fluorescent lamp power	36 W			
Ballast Compatibility	EM/Mains			
Temperature				
Ambient temperature range	-20 °C to 45 °C			
T-Case Maximum (Nom)	60 °C			
Controls and Dimming				
Dimmable	No			
Mechanical and Housing				
Bulb Finish	Frosted			


Bulb Material	Glass		
Product Length	1,200 mm		
Bulb Shape	Т8		
Approval and Application			
Energy Efficiency Class	E		
Energy Saving Product	Yes		
Approval Marks	RoHS compliance CE marking KEMA		
	Keur certificate		
Energy Consumption kWh/1000 h	18 kWh		
EPREL Registration Number	1384711		
Product Data			
Order product name	CorePro LEDtube 1200mm HO 18W 865		
	Т8		
Full product name	CorePro LEDtube 1200mm HO 18W 865		
	Т8		
Full product code	871869680611100		
Order code	929001874802		
Material Nr. (12NC)	929001874802		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8718696806111		
Numerator - Packs per outer box	10		
EAN/UPC - Case	8718696806128		

# Dimensional drawing




Product	D1	D2	A1	A2	А3
CorePro LEDtube 1200mm HO 18W	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
865 T8					

## Photometric data




Culculus Photomeries 4.5 Philips Lighting ScV. Prigo

General uniform lighting - CorePro LEDtube 1200mm HO 18W 865 T8




Light Distribution Diagram - CorePro LEDtube 1200mm HO 18W 865 T8




Spectral Power Distribution Colour - CorePro LEDtube 1200mm HO 18W 865 T8

# Lifetime





Lumen Maintenance Diagram - CorePro LEDtube 1200mm HO 18W 865 T8



Life Expectancy Diagram - CorePro LEDtube 1200mm HO 18W 865 T8


## Lifetime





Life Expectancy Diagram - CorePro LEDtube 1200mm HO 18W 865 T8

Life Expectancy Diagram - CorePro LEDtube 1200mm HO 18W 865 T8



Lumen Maintenance Diagram - CorePro LEDtube 1200mm HO 18W 865 T8



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.