1

Lighting

PHILIPS

MASTER LEDtube EM/ Mains T8

MAS LEDtube 1200mm HO VWV 18W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime ensure this tube masters every demanding application.

Warnings and Safety

• NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.

Product data

General Information					
Cap-Base	G13 [Medium Bi-Pin Fluorescent]				
Nominal lifetime	60,000 hour(s)				
Switching Cycle	200,000				
Lighting Technology	LED				
EU RoHS compliant	Yes				
Light Technical					
Color Code	865 [CCT of 6500K]				
Beam Angle (Nom)	160 degree(s)				
Luminous Flux	2,100 lm				
Color Designation	Cool Daylight				
Correlated Color Temperature (Nom)	6500 K				
Luminous Efficacy (rated) (Nom)	116.00 lm/W				


Color Consistency	<6			
Color rendering index (CRI)	80			
LLMF At End Of Nominal Lifetime (Nom) 70 %				
Operating and Electrical				
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz			
Power Consumption	18 W			
Lamp Current (Max)	183 mA			
Lamp Current (Min)	69 mA			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.90			

MASTER LEDtube EM/Mains T8


Voltage (Nom)	100-277 V				
Temperature					
Ambient temperature range	-20 °C to 45 °C				
T-Case Maximum (Nom)	60 °C				
Controls and Dimming					
Dimmable	No				
Mechanical and Housing					
Product Length	1,200 mm				
Bulb Shape	Т8				
Approval and Application					
Energy Saving Product	Yes				
Approval Marks	RoHS compliance CE marking UL certificate				
	KEMA Keur certificate				

Energy Consumption kWh/1000 h	18 kWh			
Product Data				
Order product name	MAS LEDtube 1200mm HO VWV 18W 865 T8			
Full product name	MAS LEDtube 1200mm HO VWV 18W 865 T8			
Full product code	871869681121400			
Order code	929001877412			
Material Nr. (12NC)	929001877412			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	8718696811214			
Numerator - Packs per outer box	10			
EAN/UPC - Case	8718696811221			

Dimensional drawing




Photometric data



Light Distribution Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8

Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HO VWV	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
18W 865 T8					




Spectral Power Distribution Colour - MAS LEDtube 1200mm HO VWV 18W 865 T8

Datasheet, 2024, March 11


MASTER LEDtube EM/Mains T8

Photometric data





General uniform lighting - MAS LEDtube 1200mm HO VWV 18W 865 T8


Lifetime


















Lumen Maintenance Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8

MASTER LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, March 11 - data subject to change