

MASTER LEDtube 600mm HO VWV 10W 865 T8 MASTER LEDtube EM/Mains T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



- Dimmable: No
- Energy Efficiency Label (EEL): A+
- Luminous Efficacy (rated) (Nom): 105.00 lm/W
- Power (Nom): 10 W



• Nominal Lifetime (Nom): 60000 h



- SAP Weight Paper Unit (Case): 0.482 kg
- SAP Weight Paper Unit (Piece): 0.020 kg



- EU REACH SVHC declaration: Yes
- EU RoHS compliant: Yes



• Net Weight (Piece): 0.115 kg

Energy efficiency ranking / External awards

