



5PL-C/LED/13H/830/IF5/P/2P 20/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact flourescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data

General Information				
Cap-Base	GX23-2 [GX23-2]			
Nominal lifetime	50,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	830 [CCT of 3000K]			
Beam Angle (Nom)	150 degree(s)			
Luminous Flux	550 lm			
Color Designation	White (WH)			
Correlated Color Temperature (Nom)	3000 K			
Luminous Efficacy (rated) (Nom)	110.00 lm/W			
Color Consistency	<6			
Color rendering index (CRI)	82			
LLMF At End Of Nominal Lifetime (Nom)	70 %			
Operating and Electrical				
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz			
Power Consumption	5 W			


Lamp Current (Max)	50 mA			
Lamp Current (Min)	15 mA			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			
Voltage (Nom)	120-277 V			
UL Type	Type A - works on ballast			
Temperature				
Ambient temperature range	-4 °F to 113 °F			
T-Case Maximum (Nom)	158 °F			
Controls and Dimming				
Dimmable	No			
Mechanical and Housing				
Bulb Material	Plastic			
Product Length	5-9/16 inch			
Bulb Shape	Tube, single-ended			
Approval and Application				
Energy Saving Product	Yes			

Datasheet, 2023, November 12 data subject to change

Approval Marks	UL certificate RoHS compliance		
Energy Consumption kWh/1000 h	- kWh		
Product Data			
Order product name	5PL-C/LED/13H/830/IF5/P/2P 20/1		
Full product name	5PL-C/LED/13H/830/IF5/P/2P 20/1		
Order code	532317		


Material Nr. (12NC)	929001884604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677532314
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677532319

Dimensional drawing




Product	D	D1	A1	A2	А3
5PL-	1-1/16 inch	1-1/16 inch	3-5/8 inch	4-13/16 inch	5-7/16 inch
C/LED/13H/830/IF5/P/2P					
20/1					


Photometric data









Light Distribution Diagram - 5PL-C/LED/13H/830/IF5/P/2P 20/1




General uniform lighting - 5PL-C/LED/13H/830/IF5/P/2P 20/1

Lifetime







Lumen Maintenance Diagram - 5PL-C/LED/13H/830/IF5/P/2P 20/1








Life Expectancy Diagram - 5PL-C/LED/13H/830/IF5/P/2P 20/1





Lumen Maintenance Diagram - 5PL-C/LED/13H/830/IF5/P/2P 20/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.