



5.5PL-C/LED/13H/835/IF5/P/4P 20/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact flourescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data

General Information				
Cap-Base	G24Q [G24q]			
Nominal lifetime	50,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	835 [CCT of 3500K]			
Beam Angle (Nom)	150 degree(s)			
Luminous Flux	550 lm			
Color Designation	White (WH)			
Correlated Color Temperature (Nom)	3500 K			
Luminous Efficacy (rated) (Nom)	100.00 lm/W			
Color Consistency	<6			
Color rendering index (CRI)	82			
LLMF At End Of Nominal Lifetime (Nom)	70 %			
Operating and Electrical				
Line Frequency	25000-100000 Hz			
Input Frequency	25000-100000 Hz			
Power Consumption	5.5 W			


Lamp Current (Max)	280 mA		
Lamp Current (Min)	130 mA		
Wattage Equivalent	13 W		
Starting Time (Nom)	0.5 s		
Warm-up time to 60% light	0.5 s		
Power Factor (Fraction)	0.9		
Voltage (Nom)	14-60 V		
UL Type	UL Type A		
Temperature			
Ambient temperature range	-4 °F to 113 °F		
T-Case Maximum (Nom)	167 °F		
Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Bulb Finish	Frosted		
Bulb Material	Plastic		
Product Length	5-9/16 inch		
Bulb Shape	PL-C		

Datasheet, 2023, November 3 data subject to change

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate
Energy Consumption kWh/1000 h	- kWh
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	5.5PL-C/LED/13H/835/IF5/P/4P 20/1


Full product name	5.5PL-C/LED/13H/835/IF5/P/4P 20/1		
Order code	532416		
Material Nr. (12NC)	929001885504		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	046677532413		
Numerator - Packs per outer box	20		
EAN/UPC - Case	50046677532418		


Dimensional drawing



Product	D	D1	A1	A2	А3
5.5PL-	1-1/16 inch	1-1/16 inch	3-5/8 inch	4-13/16 inch	5-7/16 inch
C/LED/13H/835/IF5/P/4P					
20/1					

Photometric data






Spectral Power Distribution Colour - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1


General uniform lighting - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1


Photometric data




Light Distribution Diagram - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1

Lifetime






Life Expectancy Diagram - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1



Lumen Maintenance Diagram - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1




Life Expectancy Diagram - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1

Life Expectancy Diagram - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1

3

Lifetime



Lumen Maintenance Diagram - 5.5PL-C/LED/13H/835/IF5/P/4P 20/1

