

PHILIPS

Eco passport

TrueForce LED Road 60-35W E27 740

TrueForce LED Public (Road – SON)

Philips LED Road lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. TrueForce LED solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce LED road lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast or reflector.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bringing wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** No
- **Energy Efficiency Class:** D
- **Lamp Luminous Efficacy EM (Nom):** 171.00 lm/W
- **Power (Rated) (Nom):** 35 W



Circularity

- **Nominal lifetime (nom.):** 50000 h



Packaging

- **SAP Weight Paper Unit (Case):** 0.550 kg
- **SAP Weight Paper Unit (Piece):** 0.007 kg



Substances

- **EU REACH restrictions compliant:** Yes
- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes



Weight & Materials

- **Net Weight (Piece):** 0.225 kg

Energy efficiency ranking / External awards



Further reading at:

<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2023 Signify Holding. All rights reserved.