



MASTER - LED HID SON-T



TForce LED Road 60-35W E27 740

Philips MASTER - LED HID SON-T lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER - LED HID SON-T solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit MASTER - LED HID SON-T lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast (for IF replacements) or reflector.

Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	E27	171.00 lm/W	
Nominal lifetime	50,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	70
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
Flux measurement reference	Sphere	Operating and Electrical	
CE mark	Yes	Line Frequency	50 Hz
EU RoHS compliant	Yes	Input Frequency	50 Hz
Light Technical		Power Consumption	35 W
Color Code	740 [CCT of 4000K]	Lamp Current (Nom)	920 mA
Luminous Flux	6,000 lm	Starting Time (Nom)	0.5 s
Color Designation	Cool White (CW)	Warm-up time to 60% light	0.5 s
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	0.9

MASTER - LED HID SON-T

Voltage (Nom)	70-80 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Others
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	35 kWh


EPREL Registration Number	403565
Product Data	
Order product name	TForce LED Road 60-35W E27 740
Full product name	TForce LED Road 60-35W E27 740
Full product code	87186968117700
Order code	929001898502
Material Nr. (12NC)	929001898502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696811177
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696811184

Dimensional drawing




Product	D	C
TForce LED Road 60-35W E27 740	61 mm	200 mm

Photometric data




Light Distribution Diagram - TForce LED Road 60-35W E27 740



Spectral Power Distribution Colour - TForce LED Road 60-35W E27 740

MASTER - LED HID SON-T


Photometric data




General Uniform Lighting - TForce LED Road 60-35W E27 740

General uniform lighting - TForce LED Road 60-35W E27 740

Lifetime



Lumen Maintenance Diagram - TForce LED Road 60-35W E27 740



Life Expectancy Diagram - TForce LED Road 60-35W E27 740

