

### MASTER LEDtube 1500mm UO 24W 830 T8 FF RCA MASTER LEDtube EM/Mains T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime ensure this tube masters every demanding application.



#### Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



#### Energy

- **Dimmable:** No
- **Luminous Efficacy (rated) (Nom):** 141.00 lm/W
- **Power (Nom):** 24 W



#### Circularity

- **Nominal Lifetime (Nom):** 50000 h



#### Packaging

- **Copy SAP Weight Paper Unit (Case):** 1.355 kg
- **Copy SAP Weight Paper Unit (Piece):** 0.050 kg



#### Substances

- **BFR policy compliant:** Yes
- **EU REACH restrictions compliant:** Yes
- **EU RoHS compliant:** Yes
- **PVC policy compliant:** Yes



#### Weight & Materials

- **Copy Net Weight (Piece):** 0.315 kg