



# MASTER LEDtube Mains T5

## MASTER LEDtube 1200mm HO 26W 830 T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! Perfectly safe, reliable & easy to install Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximize value over lifetime with high energy saving and lower maintenance costs.

### Product data


General Information		Starting Time (Nom)	
Cap-Base	G5 [ G5]		0.5 s
EU RoHS compliant	Yes	Warm Up Time to 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	50000 h	Power Factor (Nom)	0.9
Switching Cycle	200000X	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	830 [ CCT of 3000K]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	200 °	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	3600 lm	T-Storage (Max)	65 °C
Colour Temperature, horizontal (Nom)	3000 K	T-Storage (Min)	-40 °C
Color Consistency	<6	T-Case Maximum (Nom)	72.1 °C
Colour Rendering Index horiz (Nom)	80	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	No
Operating and Electrical		Mechanical and Housing	
Input Frequency	50 to 60 Hz	Bulb Material	Glass
Power (Rated) (Nom)	26 W		

# MASTER LEDtube Mains T5

Product Length	1200 mm
<b>Approval and Application</b>	
Energy Efficiency Label	A++
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	26 kWh
<b>Product Data</b>	
Full product code	871869681921000

Order product name	MASTER LEDtube 1200mm HO 26W 830 T5
EAN/UPC - Product	8718696819210
Order code	81921000
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001908502
Net Weight (Piece)	0.215 kg


## Dimensional drawing




TLED 1200mm 26W-54W 3800lm 200D 3000K G5

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm HO 26W 830 T5	15 mm	16.9 mm	1149 mm	1156.1 mm	1163.2 mm

## Photometric data




26W G5



26W G5 830 3000K


# MASTER LEDtube Mains T5

## Photometric data




26W G5 830 3000K


## Lifetime




26W G5



26W G5



26W G5



26W G5

# MASTER LEDtube Mains T5

## Lifetime



26W G5

