



# MASTER LEDtube Mains T5

## MASTER LEDtube 1500mm HO 26W 830 T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! Perfectly safe, reliable & easy to install, the Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximise value over lifetime with high energy savings and lower maintenance costs.

### Product data

General Information	
Cap base	G5 [ G5]
Nominal lifetime (nom.)	50000 h
Switching cycle	200000X
Light Technical	
Colour Code	830 [ CCT of 3.000 K]
Technical Beam Angle (Nom)	200 °
Lamp Luminous Flux 25°C EL (Nom)	3600 lm
Colour Temperature, horizontal (Nom)	3000 K
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	26 W
Starting time (nom.)	0.5 s

Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	67.4 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb material	Glass
Product length	1500 mm

# MASTER LEDtube Mains T5

## Approval and Application


Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	26 kWh

## Product Data

Full product code	871869681929600
-------------------	-----------------

Order product name	MASTER LEDtube 1500mm HO 26W 830 T5
EAN/UPC – product	8718696819296
Order code	929001908802
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001908802
Net weight (piece)	0.285 kg


## Dimensional drawing




TLED 1500mm 26W-54W 3800lm 200D 3000K G5

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1500mm HO 26W 830 T5	15 mm	16.9 mm	1449 mm	1456.1 mm	1463.2 mm

## Photometric data



26W G5




Philips Lighting B.V. Page 11

26W G5 830 3000K


# MASTER LEDtube Mains T5

## Photometric data




26W G5 830 3000K


## Lifetime




26W G5



26W G5




26W G5



26W G5

# MASTER LEDtube Mains T5

## Lifetime



26W G5

