



MASTER LEDtube Mains T5

MASTER LEDtube 1500mm HO 26W 840 T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! Perfectly safe, reliable & easy to install, the Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximise value over lifetime with high energy savings and lower maintenance costs.

Product data

General Information	
Cap base	G5 [G5]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	50000 h
Switching cycle	200000X
Light Technical	
Colour code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	200 °
Luminous flux (nom.)	3900 lm
Correlated Colour Temperature (Nom)	4000 K
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	26 W


Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	67.4 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb material	Glass

MASTER LEDtube Mains T5

Product length	1500 mm
Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	26 kWh
Product Data	
Full product code	871869681931900

Order product name	MASTER LEDtube 1500mm HO 26W 840 T5
EAN/UPC – product	8718696819319
Order code	81931900
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001908902
Net weight (piece)	0.285 kg



Dimensional drawing



Product	D1	D2	A1	A2	A3
MASTER LEDtube 1500mm HO 26W 840 T5	15 mm	16.9 mm	1449 mm	1456.1 mm	1463.2 mm

TLED 1500mm 26W-54W 3900lm 200D 4000K G5

Photometric data



26W G5 840 4000K

26W G5

MASTER LEDtube Mains T5

Photometric data



26W G5 830 3000K

Lifetime



26W G5



26W G5



26W G5



26W G5

MASTER LEDtube Mains T5

Lifetime



26W G5

