



MASTER LEDtube Mains T5

MASTER LEDtube 1500mm HO 26W 840 T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! Perfectly safe, reliable & easy to install Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximize value over lifetime with high energy saving and lower maintenance costs.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	G5 [G5]	Warm Up Time to 60% Light (Nom)	0.5 s	
EU RoHS compliant	Yes	Power Factor (Nom)	0.9	
Nominal Lifetime (Nom)	50000 h	Voltage (Nom)	220-240 V	
Switching Cycle	200000X	Temperature		
Light Technical		T-Ambient (Max)	45 °C	
Color Code	840 [CCT of 4000K]	T-Ambient (Min)	-20 °C	
Beam Angle (Nom)	200 °	T-Storage (Max)	65 °C	
Luminous Flux (Nom)	3900 lm	T-Storage (Min)	-40 °C	
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	67.4 °C	
Color Consistency	<6	Controls and Dimming		
Color Rendering Index (Nom)	80	Dimmable	No	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Mechanical and Housing		
Operating and Electrical		Bulb Material	Glass	
Input Frequency	50 to 60 Hz			
Power (Nom)	26 W			

MASTER LEDtube Mains T5

Product Length	1500 mm
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	26 kWh
Product Data	
Full product code	871869681931900

Order product name	MASTER LEDtube 1500mm HO 26W 840 T5
EAN/UPC - Product	8718696819319
Order code	929001908902
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001908902
Net Weight (Piece)	0.285 kg



Dimensional drawing



Product	D1	D2	A1	A2	A3
MASTER LEDtube 1500mm HO 26W 840 T5	15 mm	16.9 mm	1449 mm	1456.1 mm	1463.2 mm

TLED 1500mm 26W-54W 3900lm 200D 4000K G5

Photometric data



26W G5 840 4000K

26W G5

MASTER LEDtube Mains T5

Photometric data



26W G5 830 3000K

Lifetime



26W G5



26W G5



26W G5



26W G5

MASTER LEDtube Mains T5

Lifetime



26W G5

