



TrueForce High Lumen PAR

25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

Product data


General Information		Power (Rated) (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]		25.5 W
Nominal Lifetime (Nom)	25000 h	Lamp Current (Max)	230 mA
Switching Cycle	50000X	Lamp Current (Min)	115 mA
Technical Type	25.5-75W	Wattage Equivalent	75 W
		Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.8
		Voltage (Nom)	120-277 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	95 °C
Beam Angle (Nom)	15 °		
Luminous Flux (Nom)	2500 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	2500 lm	Dimmable	No
Luminous Intensity (Nom)	16000 cd		
Color Designation	White (WH)	Approval and Application	
Rated Beam Angle	15 °	Suitable For Accent Lighting	Yes
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	98.00 lm/W	Product Data	
Color Consistency	<4	Order product name	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB
Color Rendering Index (Nom)	80	EAN/UPC - Product	046677534646
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Input Frequency	50 to 60 Hz		

TrueForce High Lumen PAR

Order code	534644
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001917004

Net Weight (Piece)	0.290 kg
--------------------	----------


Dimensional drawing




PAR30L 27.5-W 2300lm 15D 3000K E26 ND

Product	D	C
25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	96 mm	119 mm


Photometric data



LEDspot PAR30 1FB




LEDspot 25,5 PAR30L 830 S15




LEDspot 25,5 PAR30L 830 S15

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB



LEDspot PAR30 1FB

