



TrueForce High Lumen PAR

25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	25.5-75W

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	15 °
Initial lumen (Nom)	2500 lm
Luminous Intensity (Nom)	16000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	98.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	25.5 W

Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120-277 V

Temperature	
T-Case Maximum (Nom)	95 °C

Controls and Dimming	
Dimmable	No


Approval and Application	
Suitable For Accent Lighting	Yes

Product Data	
Order product name	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB
EAN/UPC - Product	046677534646
Order code	534644
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

TrueForce High Lumen PAR

Material Nr. (12NC)	929001917004
Net Weight (Piece)	0.290 kg



Dimensional drawing



PAR30L 27.5-W 2300lm 15D 3000K E26 ND


Product
25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB

Photometric data



LEDspot PAR30 1FB



LEDspot 25,5 PAR30L 830 S15



LEDspot 25,5 PAR30L 830 S15

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB

LEDspot PAR30 1FB

