

MASTER Value Decorative LED bulbs

LED classic 50W A60 B22 FL GOLD D SRT4

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

Product data

General Information	
Cap-Base	B22 [B22]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	822 [CCT of 2200K]
Luminous Flux	630 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2200 K
Luminous Efficacy (rated) (Nom)	78.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	52 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	Yes

MASTER Value Decorative LED bulbs

Mechanical and Housing	
Bulb Finish	Amber
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	LED classic 50W A60 B22 FL GOLD D SRT4
Full product name	LED classic 50W A60 B22 FL GOLD D SRT4


Full product code	871869670916001
Order code	929001921701
Material Nr. (12NC)	929001921701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696709160
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696841532

Dimensional drawing




Product	D	C
LED classic 50W A60 B22 FL GOLD D SRT4	60 mm	102 mm

Photometric data




Light Distribution Diagram - LED classic 50W A60 B22 FL GOLD D SRT4



Spectral Power Distribution Colour - LED classic 50W A60 B22 FL GOLD D SRT4


MASTER Value Decorative LED bulbs

Photometric data




General uniform lighting - LED classic 50W A60 B22 FL GOLD D SRT4

Lifetime



Life Expectancy Diagram - LED classic 50W A60 B22 FL GOLD D SRT4



Lumen Maintenance Diagram - LED classic 50W A60 B22 FL GOLD D SRT4

