

PHILIPS

Eco passport

MASTER LEDtube 1500mm HO 18.2W 840 T8 MASTER LEDtube EM/Mains

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lamping in general lighting applications.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- Dimmable: No
- Energy efficiency label (EEL): A++
- Lamp Luminous Efficacy EM (Nom): 170.00 lm/W
- Power (Rated) (Nom): 18.2 W



Circularity

- Nominal lifetime (nom.): 60000 h



Packaging

- SAP Weight Paper Unit (Case): 1.350 kg
- SAP Weight Paper Unit (Piece): 0.035 kg



Substances

- EU RoHS compliant: Yes



Weight & Materials

- SAP net weight (piece): 0.450 kg

Energy efficiency ranking / External awards



Further reading at:

<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2021 Signify Holding. All rights reserved.