



MASTER LEDtube EM/ Mains T8

MASTER LEDtube 1500mm UO 24W 865 T8 G

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Warnings and Safety

• -

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	3,700 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	154.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	24 W
Lamp Current (Max)	112 mA
Lamp Current (Min)	103 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 °C

MASTER LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1,500 mm
Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	24 kWh


Product Data	
Order product name	MAS LEDtube 1500mm UO 24W 865 T8 G
Full product name	MASTER LEDtube 1500mm UO 24W 865 T8 G
Full product code	871869959514200
Order code	59514200
Material Nr. (12NC)	929001923902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699595142
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699595159

Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm UO 24W 865 T8 G	25.8 mm	28 mm	1,498.7 mm	1,505.8 mm	1,512.9 mm

Photometric data




Light Distribution Diagram - MAS LEDtube 1500mm UO 24W 865 T8 G



Spectral Power Distribution Colour - MAS LEDtube 1500mm UO 24W 865 T8 G

MASTER LEDtube EM/Mains T8


Photometric data




General uniform lighting - MAS LEDtube 1500mm UO 24W 865 T8 G

General uniform lighting - MAS LEDtube 1500mm UO 24W 865 T8 G


Lifetime




Lumen Maintenance Diagram - MAS LEDtube 1500mm UO 24W 865 T8 G



Life Expectancy Diagram - MAS LEDtube 1500mm UO 24W 865 T8 G




Life Expectancy Diagram - MAS LEDtube 1500mm UO 24W 865 T8 G



Lumen Maintenance Diagram - MAS LEDtube 1500mm UO 24W 865 T8 G

MASTER LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAS LEDtube 1500mm UO 24W 865 T8 G

