




MASTER Value Decorative LED bulbs

LEDClassic 50W G93 E27 2200K GOLD D

The new collection of MASTER Value Decorative LED bulbs will transform any home. decorative LED bulbs are ideal for decorative lighting projects, they offer a perfect blend of (warm) white light and a minimalistic lighting experience. With a very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you can enjoy soft and evenly distributed light. And thanks to the dimmable LED bulbs, you can dial it up or down to suit your mood. So, you can create a welcoming harmony in your space with decorative LED lamps that shine with trendy and stylish charm.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	822 [CCT of 2200K]
Luminous Flux	630 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2200 K
Luminous Efficacy (rated) (Nom)	78.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	52 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	45 °C

MASTER Value Decorative LED bulbs

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Amber
Bulb Shape	G93 [G 93mm]
Approval and Application	
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	LEDClassic 50W G93 E27 2200K GOLD D



Full product name	LEDClassic 50W G93 E27 2200K GOLD D
Full product code	871869959337700
Order code	929001935201
Material Nr. (12NC)	929001935201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699593377
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699593384

Dimensional drawing



Product	D	C
LEDClassic 50W G93 E27 2200K GOLD D	95 mm	137 mm

Photometric data




Light Distribution Diagram - LEDClassic 50W G93 E27 2200K GOLD D

Spectral Power Distribution Colour - LEDClassic 50W G93 E27 2200K GOLD D


MASTER Value Decorative LED bulbs

Photometric data



General uniform lighting - LEDClassic 50W G93 E27 2200K GOLD D

Lifetime



Life Expectancy Diagram - LEDClassic 50W G93 E27 2200K GOLD D

Lumen Maintenance Diagram - LEDClassic 50W G93 E27 2200K GOLD D

