



LED Designer Deco

7.5A50/VIN/820/CL/G/DIM 2/1CT

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings


Product data

| General Information | |
|---------------------------------------|------------------------------------|
| Base | E26 [Single Contact Medium Screw] |
| RoHS mark | RoHS mark |
| Nominal Lifetime (Nom) | 15000 h |
| Switching Cycle | 20000X |
| Technical Type | 7.5-40W |
| Light Technical | |
| Color Code | 820 [CCT of 2000K] |
| Initial lumen (Nom) | 400 lm |
| Luminous Flux (Rated) (Nom) | 400 lm |
| Color Designation | Flame |
| Correlated Color Temperature (Nom) | 2000 K |
| Luminous Efficacy (rated) (Nom) | 53.00 lm/W |
| Color Consistency | <6 |
| Color Rendering Index (Nom) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 7.5 W |
| Lamp Current (Nom) | 70 mA |

| Wattage Equivalent | 40 W |
|---------------------------------|-------------------------------|
| Starting Time (Nom) | 0.5 s |
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.7 |
| Voltage (Nom) | 120 V |
| Temperature | |
| T-Case Maximum (Nom) | 45 °C |
| Controls and Dimming | |
| Dimmable | Yes |
| Product Data | |
| Order product name | 7.5A50/VIN/820/CL/G/DIM 2/1CT |
| EAN/UPC - Product | 046677536275 |
| Order code | 536276 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 2 |
| Material Nr. (12NC) | 929001936403 |
| Net Weight (Piece) | 0.230 kg |

LED Designer Deco


Dimensional drawing




Bulb A160 120V 8-40W 450lm 2000K E26 D

| Product | D | C |
|-------------------------------|--------|--------|
| 7.5A50/VIN/820/CL/G/DIM 2/1CT | 160 mm | 292 mm |


Photometric data



LEDbulb E26 40W





LEDbulb E26 G63 40W



LEDbulb E26 A50 40W

Lifetime



LEDbulb E26 D

LEDbulb E26 D

