



# LED Designer Deco

## 7.5G63/modern/840/CL/G/D+CORD black

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings


### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7.5-25W
Light Technical	
Color Code	841 [ CCT of 4100K (841)]
Initial lumen (Nom)	250 lm
Luminous Flux (Rated) (Nom)	250 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	33.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	7.5 W
Lamp Current (Nom)	70 mA
Wattage Equivalent	25 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	7.5G63/modern/840/CL/G/D+CORD black
EAN/UPC - Product	046677539696
Order code	539692
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001936695
Net Weight (Piece)	0.660 kg

# LED Designer Deco


## Dimensional drawing




Bulb G200 120V 7-40W 450lm 3500K E26 D

Product	D	C
7.5G63/modern/840/CL/G/D+CORD black	200 mm	285 mm


## Photometric data



LEDbulb E26 G63 25W





LEDbulb E26 G63 25W



LEDbulb E26 25W

## Lifetime



LEDbulb E26 D

LEDbulb E26 D

