



Classic filament LEDbulbs

7.5T20/modern/840/CL/G/DIM 1FFP

Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7.5-25W
Light Technical	
Color Code	841 [CCT of 4100K (841)]
Initial lumen (Nom)	250 lm
Luminous Flux (Rated) (Nom)	250 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	33.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	7.5 W
Lamp Current (Nom)	70 mA

Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V


Temperature	
T-Case Maximum (Nom)	45 °C

Controls and Dimming	
Dimmable	Yes

Product Data	
Order product name	7.5T20/modern/840/CL/G/DIM 1FFP
EAN/UPC - Product	046677538972
Order code	538974
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	929001936873
Net Weight (Piece)	0.196 kg

Classic filament LEDbulbs



Dimensional drawing



Product	D	C
7.5T20/modern/840/CL/G/DIM 1FFP	65 mm	272 mm


Bulb T65 120V 7-40W 450lm 3500K E26 D

Photometric data



LEDbulb E26 T20 25W


LEDbulb E26 G63 25W




LEDbulb E26 40W

Classic filament LEDbulbs

Lifetime



LEDbulb E26 D



LEDbulb E26 D

