

LED Party Bulbs

4A19/LED/RED/G/E26/ND 6/1BC

Philips A shape party lamps provided a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	Red
Color Designation	Red
Color Consistency	-
Color rendering index (CRI)	60
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	4 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Red
Bulb Material	Glass
Bulb Shape	A19
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	No
Product Data	
Order product name	4A19/LED/RED/G/E26/ND 6/1BC
Full product name	4A19/LED/RED/G/E26/ND 6/1BC
Order code	929001937003
Material Nr. (12NC)	929001937003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677538200
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677538205


LED Party Bulbs

Dimensional drawing



Product	D	C
4A19/LED/RED/G/E26/ND 6/1BC	60 mm	106 mm

Photometric data





OSRAM Research Ltd. Philips Lighting NV Page 1/1

Light Distribution Diagram - 4A19/LED/RED/G/E26/ND 6/1BC

General uniform lighting - 4A19/LED/RED/G/E26/ND 6/1BC

Lifetime



Life Expectancy Diagram - 4A19/LED/RED/G/E26/ND 6/1BC



Lumen Maintenance Diagram - 4A19/LED/RED/G/E26/ND 6/1BC