



# TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

## TrueForce Core HB MV ND 28-24W E27 840

Philips TrueForce Core LED I&R lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce Core LED I&R lamps and bypass the existing ballast while enhancing the lighting quality.

### Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	E27 [E27]	Color Consistency	<6
Nominal lifetime	20,000 hour(s)	Color rendering index (CRI)	80
Switching Cycle	50,000	LLMF At End Of Nominal Lifetime (Nom)	70 %
Lighting Technology	LED	Operating and Electrical	
EU RoHS compliant	Yes	Line Frequency	50 to 60 Hz
Light Technical		Input Frequency	50 to 60 Hz
Color Code	840 [CCT of 4000K]	Power Consumption	24 W
Beam Angle (Nom)	240 degree(s)	Lamp Current (Nom)	250 mA
Luminous Flux	2,800 lm	Starting Time (Nom)	0.5 s
Color Designation	Cool White (CW)	Warm-up time to 60% light	0.5 s
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	0.5

TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T-shape
Approval and Application	
Energy Consumption kWh/1000 h	24 kWh



Product Data	
Order product name	TForce Core HB MV ND 28-24W E27 840
Full product name	TrueForce Core HB MV ND 28-24W E27 840
Full product code	871869959730600
Order code	59730600
Material Nr. (12NC)	929001937702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699597306
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699597313

Dimensional drawing



Product	D	C
TForce Core HB MV ND 28-24W E27 840	105 mm	190 mm

Photometric data




General uniform lighting - TForce Core HB MV ND 28-24W E27 840

Spectral Power Distribution Colour - TForce Core HB MV ND 28-24W E27 840


# TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

## Photometric data




Light Distribution Diagram - TForce Core HB MV ND 28-24W E27 840

## Lifetime



Life Expectancy Diagram - TForce Core HB MV ND 28-24W E27 840



Lumen Maintenance Diagram - TForce Core HB MV ND 28-24W E27 840

