



# MasterClass Plastic (WarmGlow) A-Shape Lamps

## 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

Provides a wide variety of premium features, such as best-in-class warm glow dimmability, 25,000 hours long lifetime, and Title 20 certification, ideal for decorative and ambient lighting in high-end retail outlets, hotels, and restaurants.

### Product data


General Information		Operating and Electrical	
Cap-Base	E26 [Single Contact Medium Screw]	Line Frequency	60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	60 Hz
Switching Cycle	50,000	Power Consumption	8.8 W
Lighting Technology	LED	Lamp Current (Nom)	80 mA
EU RoHS compliant	Yes	Wattage Equivalent	60 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	922-927 [CCT of 2200K-2700K]	Warm-up time to 60% light	0.5 s
Beam Angle (Nom)	250 degree(s)	Power Factor (Fraction)	0.7
Luminous Flux	800 lm	Voltage (Nom)	120 V
Color Designation	Warm White (WW)	Temperature	
Correlated Color Temperature (Nom)	2200 2700 K	T-Case Maximum (Nom)	80 °C
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Controls and Dimming	
Color Consistency	<4	Dimmable	Yes
Color rendering index (CRI)	90	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted

# MasterClass Plastic (WarmGlow) A-Shape Lamps

Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
<b>Approval and Application</b>	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	Yes
<b>Application Conditions</b>	
can it be used in closed luminaires	Yes



<b>Product Data</b>	
Order product name	8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT
Full product name	8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT
Order code	929001940904
Material Nr. (12NC)	929001940904
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677479442
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677479447

## Dimensional drawing



Product	D	C
8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT	62.5 mm	111.5 mm

## Photometric data




Spectral Power Distribution Colour - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

General uniform lighting - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT


# MasterClass Plastic (WarmGlow) A-Shape Lamps

## Photometric data




Light Distribution Diagram - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

## Lifetime



Life Expectancy Diagram - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT



Lumen Maintenance Diagram - 8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT

