



A-Shape LED

12.2A21/PER/927-22/P/E26/WG 6/1FB T20

Philips A-Shape Dimmable LED Lamps are the smart LED Alternative to standard incandescent. The unique lamp design provides omni-directional light with excellent dimming performance.


Product data

General information		Warm Up Time to 60% Light (Nom)	
Base	E26 [Single Contact Medium Screw]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.7
Nominal Lifetime (Nom)	15000 h	Voltage (Nom)	120 V
Switching Cycle	50000X	Temperature	
Technical Type	12.2-75W	T-Case Maximum (Nom)	75 °C
Light technical		Controls and dimming	
Color Code	922-927 [CCT of 2200K-2700K]	Dimmable	Yes
Beam Angle (Nom)	250 °	Mechanical and housing	
Initial lumen (Nom)	1100 lm	Bulb Finish	Frosted
Color Designation	Warm White (WW)	Bulb Material	Plastic
Correlated Color Temperature (Nom)	- K	Bulb Shape	A21 (A21)
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Approval and application	
Color Consistency	<4	Energy Consumption kWh/1000 h	- kWh
Color Rendering Index (Nom)	90	Product data	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order product name	12.2A21/PER/927-22/P/E26/WG 6/1FB T20
Operating and electrical		EAN/UPC - Product	046677479466
Input Frequency	60 Hz	Order code	479469
Power (Rated) (Nom)	12.2 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	115 mA	Numerator - Packs per outer box	6
Wattage Equivalent	75 W		
Starting Time (Nom)	0.5 s		

A-Shape LED

Material Nr. (12NC)	929001941104
Net Weight (Piece)	0.174 kg


Dimensional drawing




12.2A21/PER/927-22/P/E26/WG 6/1FB T20

Product	D	C
12.2A21/PER/927-22/P/E26/WG 6/1FB T20	78 mm	140 mm


Photometric data



LED Bulb A21 E26 12.2-75W





LED Bulb A21 E26 12.2-75W



LED Bulb A21 E26 12.2-75W

A-Shape LED

Lifetime



LEDBulb E26

LEDBulb E26

