



# A-Shape LED

## 12.2A21/PER/927-22/P/E26/WG 6/1FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.



### Product data

General Information		Warm-up time to 60% light	
Cap-Base	E26 [Single Contact Medium Screw]		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)	0.7
Switching Cycle	50,000	Voltage (Nom)	120 V
Lighting Technology	LED	<b>Temperature</b>	
EU RoHS compliant	Yes	T-Case Maximum (Nom)	167 °F
<b>Light Technical</b>		<b>Controls and Dimming</b>	
Color Code	922-927 [CCT of 2200K-2700K]	Dimmable	Yes
Beam Angle (Nom)	250 degree(s)	<b>Mechanical and Housing</b>	
Luminous Flux	1,100 lm	Bulb Finish	Frosted
Color Designation	Warm White (WW)	Bulb Material	Plastic
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Shape	A21 [A 21mm]
Color Consistency	<4	<b>Approval and Application</b>	
Color rendering index (CRI)	90	Energy Consumption kWh/1000 h	- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Product Data</b>	
<b>Operating and Electrical</b>		Order product name	12.2A21/PER/927-22/P/E26/WG 6/1FB T20
Line Frequency	60 Hz	Full product name	12.2A21/PER/927-22/P/E26/WG 6/1FB T20
Input Frequency	60 Hz	Order code	479469
Power Consumption	12.2 W	Material Nr. (12NC)	929001941104
Lamp Current (Nom)	115 mA	Numerator - Quantity Per Pack	1
Wattage Equivalent	75 W		
Starting Time (Nom)	0.5 s		



# A-Shape LED

## Lifetime



Life Expectancy Diagram - 12.2A21/PER/927-22/P/E26/WG 6/1FB T20

Lumen Maintenance Diagram - 12.2A21/PER/927-22/P/E26/WG 6/1FB T20

