

PHILIPS

Eco passport

LEDClassic 4-35W A60 E27 825 CL _G NDAPR Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- Dimmable: No
- Energy Efficiency Label (EEL): A++
- Luminous Efficacy (rated) (Nom): 100.00 lm/W
- Power (Nom): 4 W

Circularity

- Nominal Lifetime (Nom): 15000 h

Packaging

- SAP Weight Paper Unit (Case): 0.541 kg
- SAP Weight Paper Unit (Piece): 0.026 kg

Substances

- EU REACH restrictions compliant: Yes
- EU RoHS compliant: Yes

Weight & Materials

- Net Weight (Piece): 0.034 kg

Energy efficiency ranking / External awards



Further reading at:
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2021 Signify Holding. All rights reserved.