



Classic filament LEDbulbs

LEDClassic 5.5-48W A60 E27 825 CL_G NDCN

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	5.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	50 mA
Switching Cycle	20,000	Wattage Equivalent	48 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.51
Color Code	825 [CCT of 2500K]	Voltage (Nom)	220-240 V
Luminous Flux	600 lm	Temperature	
Color Designation	Warm White (WW)	T-Case Maximum (Nom)	55 °C
Correlated Color Temperature (Nom)	2500 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	109.00 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Transparent amber
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A60 [A 60mm]
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	LEDClassic 5.5-48W A60 E27 825 CL_G NDCN
Full product name	LEDClassic 5.5-48W A60 E27 825 CL_G NDCN
Full product code	694793914782300
Order code	929001941710


Material Nr. (12NC)	929001941710
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6947939147823
Numerator - Packs per outer box	10
EAN/UPC - Case	6947939147830

Dimensional drawing




Product	D	C
LEDClassic 5.5-48W A60 E27 825 CL_G NDCN	60 mm	106 mm

Photometric data



General uniform lighting - LEDClassic 5.5-48W A60 E27 825 CL_G NDCN

Spectral Power Distribution Colour - LEDClassic 5.5-48W A60 E27 825 CL_G NDCN



Light Distribution Diagram - LEDClassic 5.5-48W A60 E27 825 CL_G NDCN

Classic filament LEDbulbs

Lifetime

Life Expectancy Diagram - LEDClassic 5.5-48W A60 E27 825 CL_G NDCN

Lumen Maintenance Diagram - LEDClassic 5.5-48W A60 E27 825 CL_G NDCN

