


PHILIPS

Eco passport

LEDClassic 5.5-48W ST64 E27 825CL_GNDAPR Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- Dimmable: No
- Energy efficiency label (EEL): A++
- Lamp Luminous Efficacy EM (Nom): 109.00 lm/W
- Power (Rated) (Nom): 5.5 W

Circularity

- Nominal lifetime (nom.): 15000 h

Packaging

- SAP Weight Paper Unit (Case): 0.930 kg
- SAP Weight Paper Unit (Piece): 0.010 kg

Substances

- EU RoHS compliant: Yes

Weight & Materials

- Net weight (piece): 0.046 kg

Energy efficiency ranking / External awards



Further reading at:
<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2020 Signify Holding. All rights reserved.