

# LED Designer Deco

## 5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

### Product data

<b>General Information</b>	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

<b>Light Technical</b>	
Color Code	820 [CCT of 2000K]
Luminous Flux	350 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	70.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

<b>Operating and Electrical</b>	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

<b>Temperature</b>	
T-Case Maximum (Nom)	52 °C

<b>Controls and Dimming</b>	
Dimmable	Yes

<b>Mechanical and Housing</b>	
Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	ST19


<b>Approval and Application</b>	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	No
EyeComfort	Yes

<b>Product Data</b>	
Order product name	5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20
Full product name	5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20
Order code	929001951033
Material Nr. (12NC)	929001951033

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677556808
Numerator - Packs per outer box	4



EAN/UPC - Case	50046677556803
----------------	----------------

Dimensional drawing




Product	D	C
5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20	64 mm	138 mm

Photometric data



Light Distribution Diagram - 5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20

General uniform lighting - 5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20



Spectral Power Distribution Colour - 5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20

Lifetime



Life Expectancy Diagram - 5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20



Lumen Maintenance Diagram - 5ST19/VIN/820/E26/CL/GL/DIM 4/1FBH T20

