



A-Shape LED

10A19/LED/827/FR/P/ND 4/4FB

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data

General Information		Warm Up Time to 60% Light (Nom)	
Base	E26 [Single Contact Medium Screw]		0.5 s
Nominal Lifetime (Nom)	11000 h	Power Factor (Nom)	0.5
Switching Cycle	50000X	Voltage (Nom)	120 V
Technical Type	10-60 W		
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	85 °C
Beam Angle (Nom)	150 °		
Initial lumen (Nom)	800 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	800 lm	Dimmable	No
Color Designation	Warm White (WW)		
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	80.00 lm/W	Bulb Finish	Frosted
Color Consistency	<6		
Color Rendering Index (Nom)	80	Product Data	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order product name	10A19/LED/827/FR/P/ND 4/4FB
		EAN/UPC - Product	50046677461121
		Order code	461129
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	4
		Material Nr. (12NC)	929001957633
		Net Weight (Piece)	0.055 kg
Operating and Electrical			
Input Frequency	60 Hz		
Power (Rated) (Nom)	10 W		
Lamp Current (Nom)	165 mA		
Wattage Equivalent	60 W		
Starting Time (Nom)	0.5 s		

A-Shape LED


Dimensional drawing




Bulb A60 120V 10-60W 800lm 2700K E26 ND

Product	D	C
10A19/LED/827/FR/P/ND 4/4FB	60 mm	110 mm

Photometric data




LedBulb A19 E26 11W



CalcULX Photometrics 4.5 Philips Lighting B.V. Page: 1/7


LedBulb A19 E26 11W




LedBulb A19 E26

A-Shape LED

Lifetime



LedBulb A19 E26



LedBulb A19 E26

