



A-Shape LED

11A19/LED/827/FR/P/ND 4/6FB

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	72.00 lm/W
Color Consistency	ANSI
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	11 W
Lamp Current (Nom)	165 mA
Wattage Equivalent	60 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19 [A 19mm]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	11A19/LED/827/FR/P/ND 4/6FB
Full product name	11A19/LED/827/FR/P/ND 4/6FB
Order code	455592
Material Nr. (12NC)	929001957675
Numerator - Quantity Per Pack	1

A-Shape LED



EAN/UPC - Product/Case	046677455590
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677455595

Dimensional drawing




Product	D	C
11A19/LED/827/FR/P/ND 4/6FB	60 mm	110 mm

Photometric data



Spectral Power Distribution Colour - 11A19/LED/827/FR/P/ND 4/6FB


General uniform lighting - 11A19/LED/827/FR/P/ND 4/6FB




Light Distribution Diagram - 11A19/LED/827/FR/P/ND 4/6FB

A-Shape LED

Lifetime



Life Expectancy Diagram - 11A19/LED/827/FR/P/ND 4/6FB



Lumen Maintenance Diagram - 11A19/LED/827/FR/P/ND 4/6FB

