



LED A19-A21

9A19/LED/850/FR/P/ND 4/2FB

Philips A19/A21 LED lamps are the smart alternative to standard incandescent. The unique lamp design provides omni-directional light with excellent dimming performance.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	11000 h
Switching Cycle	50000X
Technical Type	9-60W
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	150 °
Initial lumen (Nom)	800 lm
Luminous Flux (Rated) (Nom)	800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	88.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	9 W
Lamp Current (Nom)	150 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Product Data	
Order product name	9A19/LED/850/FR/P/ND 4/2FB
EAN/UPC - Product	50046677548235
Order code	548230
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001958004
Net Weight (Piece)	0.042 kg

LED A19-A21


Dimensional drawing




Bulb A60 120V 10-60W 800lm 5000K E26 ND

Product	D	C
9A19/LED/850/FR/P/ND 4/2FB	60 mm	110 mm

Photometric data




LedBulb A19 E26



CalcULX Photometrics 4.5 Philips Lighting B.V. Page: 1/7

LedBulb A19 E26 11W 850



LedBulb A19 E26

LED A19-A21

Lifetime



LedBulb A19 E26



LedBulb A19 E26

