Lighting

PHILIPS

Contractor-grade InstantFit (UL Type-A) T8

16T8/LED/48-850/IF18/G 25/1

The InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect .Other lamps claim compatibility but only InstantFit (UL Type A) has been proven to work with over 350 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy the InstantFit lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data

General Information					
Cap-Base	G13 [Medium Bi-Pin Fluorescent]				
Nominal lifetime	36,000 hour(s)				
Switching Cycle	50,000				
Lighting Technology	LED				
EU RoHS compliant	Yes				
Light Technical					
Color Code	850 [CCT of 5000K]				
Beam Angle (Nom)	240 degree(s)				
Luminous Flux	1,800 lm				
Color Designation	Daylight				

Correlated Color Temperature (Nom)	5000 K		
Luminous Efficacy (rated) (Nom)	112.00 lm/W		
Color Consistency	<6		
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	20K to 120K Hz		
Input Frequency	20K to 120K Hz		
Power Consumption	16 W		
Lamp Current (Max)	330 mA		
Lamp Current (Min)	110 mA		

Contractor-grade InstantFit (UL Type-A) T8

Wattage Equivalent	32 W				
Starting Time (Nom)	0.5 s				
Warm-up time to 60% light	0.5 s				
Power Factor (Fraction)	0.9				
Voltage (Nom)	120-277, 347 V				
UL Type	UL Type A				
Temperature					
Ambient temperature range	-20 °C to 45 °C				
T-Case Maximum (Nom)	35 ℃				
Controls and Dimming					
Dimmable	No				
Mechanical and Housing					
Bulb Finish	Frosted				
Bulb Material	Glass				
Product Length	1,200 mm				
Bulb Shape	T8				

Approval and Application					
Energy Saving Product	Yes				
Approval Marks	RoHS compliance UL certificate				
Energy Consumption kWh/1000 h	- kWh				
Application Conditions					
can it be used in closed luminaires	Yes				
Product Data					
Order product name	16T8/LED/48-850/IF18/G 25/1				
Full product name	16T8/LED/48-850/IF18/G 25/1				
Order code	542092				
Material Nr. (12NC)	929001960704				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	046677542092				
Numerator - Packs per outer box	25				
EAN/UPC - Case	50046677542097				

Dimensional drawing



Product	D1	D2	A1	A2	A3
16T8/LED/48-850/IF18/G 25/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Photometric data





Light Distribution Diagram - 16T8/LED/48-850/IF18/G 25/1

Contractor-grade InstantFit (UL Type-A) T8

Photometric data



Spectral Power Distribution Colour - 16T8/LED/48-850/IF18/G 25/1

Lifetime



Life Expectancy Diagram - 16T8/LED/48-850/IF18/G 25/1







100

80





Contractor-grade InstantFit (UL Type-A) T8



Lumen Maintenance Diagram - 16T8/LED/48-850/IF18/G 25/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 14 - data subject to change