

# Contractor-grade InstantFit (UL Type-A) T8

## 16T8/LED/48-850/IF18/G 25/1

The InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect .Other lamps claim compatibility but only InstantFit (UL Type A) has been proven to work with over 350 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy the InstantFit lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

#### **Product data**

| General Information |                                 |
|---------------------|---------------------------------|
| Cap-Base            | G13 [Medium Bi-Pin Fluorescent] |
| Nominal lifetime    | 36,000 hour(s)                  |
| Switching Cycle     | 50,000                          |
| Lighting Technology | LED                             |
| EU RoHS compliant   | Yes                             |
|                     |                                 |
| Light Technical     |                                 |
| Color Code          | 850 [CCT of 5000K]              |
| Beam Angle (Nom)    | 240 degree(s)                   |
| Luminous Flux       | 1,800 lm                        |
| Color Designation   | Daylight                        |

| Correlated Color Temperature (Nom)    | 3000 K         |
|---------------------------------------|----------------|
| Luminous Efficacy (rated) (Nom)       | 112.00 lm/W    |
| Color Consistency                     | <6             |
| Color rendering index (CRI)           | 80             |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %           |
|                                       |                |
| Operating and Electrical              |                |
| Line Frequency                        | 20K to 120K Hz |
| Input Frequency                       | 20K to 120K Hz |
| Power Consumption                     | 16 W           |
| Lamp Current (Max)                    | 330 mA         |
| Lamp Current (Min)                    | 110 mA         |

5000 K

Correlated Color Temperature (Nom)


Datasheet, 2023, October 27 data subject to change

# Contractor-grade InstantFit (UL Type-A) T8

| Wattage Equivalent        | 32 W            |
|---------------------------|-----------------|
| Starting Time (Nom)       | 0.5 s           |
| Warm-up time to 60% light | 0.5 s           |
| Power Factor (Fraction)   | 0.9             |
| Voltage (Nom)             | 120-277, 347 V  |
| UL Type                   | UL Type A       |
|                           |                 |
| Temperature               |                 |
| Ambient temperature range | -4 °F to 113 °F |
| T-Case Maximum (Nom)      | 95 °F           |
|                           |                 |
| Controls and Dimming      |                 |
| Dimmable                  | No              |
|                           |                 |
| Mechanical and Housing    |                 |
| Bulb Finish               | Frosted         |
| Bulb Material             | Glass           |
| Product Length            | 47-1/4 inch     |
| Bulb Shape                | Т8              |
|                           |                 |

| Approval and Application            |                                |
|-------------------------------------|--------------------------------|
| Energy Saving Product               | Yes                            |
| Approval Marks                      | RoHS compliance UL certificate |
| Energy Consumption kWh/1000 h       | - kWh                          |
| Application Conditions              |                                |
| can it be used in closed luminaires | Yes                            |
|                                     |                                |
| Product Data                        |                                |
| Order product name                  | 16T8/LED/48-850/IF18/G 25/1    |
| Full product name                   | 16T8/LED/48-850/IF18/G 25/1    |
| Order code                          | 542092                         |
| Material Nr. (12NC)                 | 929001960704                   |
| Numerator - Quantity Per Pack       | 1                              |
| EAN/UPC - Product/Case              | 046677542092                   |
| Numerator - Packs per outer box     | 25                             |
| EAN/UPC - Case                      | 50046677542097                 |

## Dimensional drawing




 Product
 D1
 D2
 A1
 A2
 A3


 16T8/LED/48-850/IF18/G
 1-1/16 inch
 1-1/8 inch
 47-3/16 inch
 47-1/2 inch
 47-3/4 inch

 25/1

## Photometric data




Accent Lighting Spots - 16T8/LED/48-850/IF18/G 25/1



Light Distribution Diagram - 16T8/LED/48-850/IF18/G 25/1


## Contractor-grade InstantFit (UL Type-A) T8


#### Photometric data




Spectral Power Distribution Colour - 16T8/LED/48-850/IF18/G 25/1

### Lifetime






## Life Expectancy Diagram - 16T8/LED/48-850/IF18/G 25/1



Life Expectancy Diagram - 16T8/LED/48-850/IF18/G 25/1




Lumen Maintenance Diagram - 16T8/LED/48-850/IF18/G 25/1

Life Expectancy Diagram - 16T8/LED/48-850/IF18/G 25/1

# Contractor-grade InstantFit (UL Type-A) T8

### Lifetime



Lumen Maintenance Diagram - 16T8/LED/48-850/IF18/G 25/1

