

# MasterClass InstantFit (UL Type-A) T8

### 8.5T8/MAS/36-840/IF14/P/DIM 10/1

The MasterClass InstantFit T8 lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only MasterClass InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the MasterClass InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system. With available 70,000 hour life, 7-year limited warranty and a shatter-prevention polycarbonate lens, Philips MasterClass InstantFit TLED lamps deliver benefits for all.

#### **Product data**

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Nominal lifetime	70,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	840 [CCT of 4000K]			

Beam Angle (Nom)	180 degree(s)			
Luminous Flux	1,400 lm			
Color Designation	Cool White (CW)			
Correlated Color Temperature (Nom)	4000 K			
Luminous Efficacy (rated) (Nom)	164 lm/W			
Color Consistency	<6			
Color rendering index (CRI)	80			
LLMF At End Of Nominal Lifetime (Nom) 70 %				


Datasheet, 2024, January 4 data subject to change

## MasterClass InstantFit (UL Type-A) T8

Operating and Electrical					
Line Frequency	20K to 120K Hz				
Input Frequency	20K to 120K Hz				
Power Consumption	8.5 W				
Lamp Current (Max)	280 mA				
Lamp Current (Min)	50 mA				
Wattage Equivalent	25 W				
Starting Time (Nom)	0.5 s				
Warm-up time to 60% light	0.5 s				
Power Factor (Fraction)	0.9				
Voltage (Nom)	120-277,347 V				
UL Type	UL Type A				
Temperature					
Ambient temperature range	-20 °C to 45 °C				
T-Case Maximum (Nom)	40 °C				
Controls and Dimming					
Dimmable	Only with specific dimmers				
Mechanical and Housing					
Bulb Finish	Frosted				
Bulb Material	Plastic				
Product Length	900 mm				

Pulls Chaire	TO			
Bulb Shape	T8			
Approval and Application				
Energy Saving Product	Yes			
Approval Marks	RoHS compliance UL certificate DLC			
	compliance			
Energy Consumption kWh/1000 h	- kWh			
Energy Certifications	DLC Standard			
Application Conditions				
can it be used in closed luminaires	Yes			
Product Data				
Order product name	8.5T8/MAS/36-840/IF14/P/DIM 10/1			
Full product name	8.5T8/MAS/36-840/IF14/P/DIM 10/1			
Order code	929001967604			
Material Nr. (12NC)	929001967604			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	046677539870			
Numerator - Packs per outer box	10			
EAN/UPC - Case	50046677539875			


## Dimensional drawing




Product	D1	D2	A1	A2	A3
8.5T8/MAS/36-840/IF14/P/DIM	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
10/1					


## MasterClass InstantFit (UL Type-A) T8


#### Photometric data






General uniform lighting - 8.5T8/MAS/36-840/IF14/P/DIM 10/1






Light Distribution Diagram - 8.5T8/MAS/36-840/IF14/P/DIM 10/1

#### Lifetime







Life Expectancy Diagram - 8.5T8/MAS/36-840/IF14/P/DIM 10/1

Life Expectancy Diagram - 8.5T8/MAS/36-840/IF14/P/DIM 10/1

## MasterClass InstantFit (UL Type-A) T8


#### Lifetime





Lumen Maintenance Diagram - 8.5T8/MAS/36-840/IF14/P/DIM 10/1

Life Expectancy Diagram - 8.5T8/MAS/36-840/IF14/P/DIM 10/1



Lumen Maintenance Diagram - 8.5T8/MAS/36-840/IF14/P/DIM 10/1



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.