

Classic filament LEDbulbs

5A19/PER/927-922/CL/G/E26/WGX 1FB T20

Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	450 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	5 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.75
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	122 °F

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A19 [A 19mm]


Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	5A19/PER/927-922/CL/G/E26/WGX 1FB T20
Full product name	5A19/PER/927-922/CL/G/E26/WGX 1FB T20
Order code	549485
Material Nr. (12NC)	929001969504



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677549480
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677549485

Dimensional drawing




Product	D	C
5A19/PER/927-922/CL/G/E26/WGX 1FB T20	2-3/8 inch	4-1/4 inch

Photometric data



Spectral Power Distribution Colour - 5A19/PER/927-922/CL/G/E26/WGX 1FB T20


General uniform lighting - 5A19/PER/927-922/CL/G/E26/WGX 1FB T20




Light Distribution Diagram - 5A19/PER/927-922/CL/G/E26/WGX 1FB T20

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - 5A19/PER/927-922/CL/G/E26/WGX 1FB T20



Lumen Maintenance Diagram - 5A19/PER/927-922/CL/G/E26/WGX 1FB T20

